



## S8FS-C35024J

Power supply, 350 W, 100-240 VAC input, 24 VDC, 14.6 A output, Front terminal

# Specifications

Type	Metal frame
Mounting method	Direct mounting
Phase	Single
Power output	350 W
Efficiency	88 %
Output voltage	24 V
Rated output current	14.6 A
Temperature range	-20-60 °C
Features	Terminal block facing forward
Terminal	Screw
Communication port(s)	None
Alarm function	-
Number of output branches	1
Rated supply voltage at AC 50 Hz	100-240 V
Allowable supply voltage AC	90-264 V
Allowable supply voltage DC	254-373 V
Width	112.5 mm
Height	50 mm
Depth	212 mm

S82Y-FSC350DIN

Mounting bracket, DIN-rail, 75W, 200W, 350W

## Downloads

CAD Library



**S8FS-C Switching  
Power Supply**  
Datasheet

EN PDF 11 MB